



Solving SWaP-C power challenges for MIL-COTS applications

Modular solutions for your mission critical power systems

VICOR

On the forefront of power architectures

Solving the toughest aerospace and defense power delivery challenges

Vicor continues to raise the bar by delivering technologically advanced MIL-COTS power solutions that meet demanding SWaP-C requirements with all the robustness and reliability you would expect from a 40 year trusted supplier to the aerospace and defense industry. Vicor has a portfolio of highly reliable modular components that enable military equipment designers to create SWaP-C optimized solutions. A good example is our DCM™ family DC-DC converters. When compared to the next-best solutions in brick packages, our innovative ChiP and VIA packages enable solutions with upwards of 2.5X improvement in power density by volume, and over 3X the power density by weight.




HALE UAVs

High-efficiency, high-density DCM DC-DC converters double the internal bus power and keep the aircraft as light as possible



Portable digital radio

High-performance modules provide a well-regulated 48V at more than 1kW to enable higher peak RF output power




Tethered underwater vehicles

High voltage tethers allow for greater tether lengths, use smaller and lighter cabling and significantly reduce I²R losses



Advanced CSISR capabilities

Flexible, capable power delivery supports more functionality and affords UAVs increased payload and longer runtime



Electronic countermeasure

Smaller, more efficient power solutions enable improved counter measure capabilities




Enhanced missile defense

Powering your suite of advanced sensors and delivering unparalleled results

MIL-COTS DCM™ isolated-regulated DC-DC converter modules

Rugged high power converters for 28V and 270V line inputs

The DCM is an isolated, regulated DC-DC converter, operating from an unregulated, wide range input to generate an isolated output. With its high frequency zero-voltage switching (ZVS) topology, the DCM converter delivers high efficiency across its specified input line range. Modular DCM converters used independently or with downstream point-of-load (PoL) products support efficient power distribution, providing superior power system performance and connectivity from a variety of unregulated power sources to the point of load. The DCM VIA module provides a higher level of functionality with integrated EMI filtering, tight output voltage regulation and a secondary-referenced PMBus control interface. The DCM is able to meet MIL-STD-810, MIL-STD-704, MIL-STD-1275, and DO-160 when used in conjunction with the MIL-COTS MFM filter.



Features and benefits



Up to 500W,
17.86A continuous



Up to 93%
peak efficiency



Up to 1,032W/in³
power density



OV, OC, UV, short
circuit & thermal
protection

Input voltage range:

9.0 – 50.0V	16.0 – 50.0V
160.0 – 420.0V	180.0 – 400.0V

Output voltage range:

2.97 – 3.63V	3.5 – 5.5V
4.0 – 5.5V	7.2 – 13.2V
9.0 – 16.5V	14.4 – 26.4V
16.8 – 30.8V	22.0 – 30.8V
22.0 – 36.0	28.8 – 52.8V

Power:

2322 ChiP: Up to 60W	3414 VIA: Up to 320W
3623 ChiP: Up to 320W	3714 VIA: Up to 500W
4623 ChiP: Up to 500W	5614 VIA: Up to 1,300W

Dimensions:

2322 ChiP: 24.8 x 22.8 x 7.2mm
3623 ChiP: 38.7 x 22.8 x 7.2mm
4623 ChiP: 47.9 x 22.8 x 7.2mm
3414 VIA: 85.9 x 35.5 x 9.4mm
3714 VIA: 95.1 x 35.5 x 9.4mm
5614 VIA: 141.4 x 35.5 x 9.4mm

A complete list of MIL-COTS DCMs are available at vicorpower.com/mil-cots-dcm

MIL-COTS BCM® isolated fixed-ratio DC-DC bus converter modules

High-voltage bidirectional bus converters

The MIL-COTS Bus Converter Module (BCM) is a high efficiency (up to 98.7%), fixed ratio module operating from a 270V input voltage and delivering an isolated 28V or 48V nominal output voltage. The low weight, high efficiency and high power density enable our customers to meet their increasing SWaP-C requirements. The BCMs wide input range help achieve MIL-STD-704 E/F ranges without the need for external clamping. Low noise, high-frequency operation minimizes the size of the filter needed for MIL-STD compliance. The BCM enables system design flexibility and can be paralleled to create multi-kW arrays.



Features and benefits



MIL-STD-704E/F compliant



High efficiency up to 98.7%



Power density >2,342 W/in³, at 36.58W/gram



Can be paralleled to create multi-kW arrays

Input voltage range:

200 – 330V	330 – 365V
200 – 400V	360 – 400V
240 – 330V	400 – 700V
260 – 410V	500 – 800V

Output voltage range:

8.1 – 12.8V	30.0 – 41.25V
10.3 – 11.4V	31.25 – 50.0V
11.2 – 12.5V	32.5 – 51.3V
11.8 – 13.0V	33.4 - 55.1V
16.3 – 25.6V	41.3 - 45.6V
25.0 – 43.7V	45.0 - 50.0V
25.0 – 50.0V	

Current:

Full Chip: Up to 25.8A
6123 ChiP: Up to 125A
4414 VIA: Up to 125A

Dimensions:


Full Chip: 32.5 x 22.0 x 6.7mm
6123 ChiP: 63.3 x 22.8 x 7.2mm
4414 VIA: 110.6 x 35.5 x 9.4mm

A complete list of BCMs are available at vicorpower.com/mil-cots-bcm

ZVS buck and buck-boost switching non-isolated DC-DC regulators

Wide range direct to PoL regulators

This series of regulators offer board-level designers maximum power density and flexibility for high-efficiency point-of-load DC-DC regulation. High performance Zero-Voltage Switching (ZVS) topology increases point-of-load performance, providing best-in-class efficiency up to 98%. They are highly integrated with control circuitry, power semiconductors and support components in a high density System in Package (SiP). It can also be configured to operate in constant-current mode with -55°C to +125°C operation.



Features and benefits



Wide operating range



Simple to use; fast development



High efficiency of over 98%



Flexible and rich feature set

ZVS buck regulators

Input voltage range:

8.0 – 18.0V 14.0 – 42.0V 30.0 – 60.0V

8.0 – 36.0V 17.4 – 36.0V 36.0 – 60.0V

11.0 – 36.0V 20.4 – 36.0V

Output voltage range:

2.2 – 4.0V 4.0 – 5.5V 6.5 – 14.0V

2.3 – 4.1V 4.0 – 6.5V 10.0 – 16.0V

3.3 – 6.5V 6.5 – 13.0V

Current/Dimensions:

10.0 x 10.0 x 2.5mm LGA SiP: Up to 10A

10.0 x 14.0 x 2.5mm LGA SiP: Up to 22A

ZVS buck-boost regulators

Input voltage range:

8.0 – 60.0V 21.0 – 60.0V

Output voltage range:

10.0 – 50.0V 21.0 – 36.0V 36.0 – 54.0V

Power:

Up to 150W

Dimensions:

LGA SiP: 10.0 x 14.0 x 2.5mm

A complete list of buck and buck-boost regulators are available at vicorpower.com/buck and vicorpower.com/buck-boost

MIL-COTS VITA-62™

VITA-62 compliant power converters

The VITA 62 power supply is a MIL-COTS power supply that is designed for 3U Open VPX systems. This rugged, conduction-cooled model operates from a nominal 28V or 270V DC input, with predefined output voltages ranging from 3.3V to 12V, delivering up to 600W of power. Customers requiring different output voltages or power levels can request a customized power supply to meet their own specifications. This family of products has been fully tested to meet MIL-461F and MIL-704F. In addition the 28V input version also meets MIL-1275D.



Features and benefits



Scalable OpenVPX
compliant
form-factor



Over-current,
-voltage & -temp
protections



MIL-STD 704F,
461F, 810G,
1275D



No electrolytic
capacitors

Input voltage range:

18 – 42VDC

18 – 45VDC

180 – 420VDC

3-Phase AC 400Hz

Output voltage:

+12V@ 40/70A

+5V @ 30/32A

+3.3V @ 6/30A

+12V @ 1A

-12V @ 1A

+28@26.78A

Output power:

3U (600W total power)

6U (1000W total power)

3U (750W total power AC)

Dimensions:

3U (3.9 x 6.6 x 1.0in)

6U (9.2 x 6.6 x 1.0in)

A complete list of VITA-62 power supplies are available at vicorpower.com/vita-62

SOSA-aligned power supplies

The Vicor SOSA-aligned power supply is a COTs power supply that is designed for 3U Open VPX systems that are developed to the SOSA standard. The module utilizes Vicor proprietary technology to enable high efficiency and power density for this highly rugged, conduction-cooled model. Up to four power supplies can be paralleled to increase output power capability of +12V main and +3.3V auxiliary outputs with proprietary wireless current sharing. Need for conventional current-share pins are eliminated. Current share accuracy is $\pm 2A$.

Features and benefits



Scalable OpenVPX
compliant
form-factor



Over-current,
-voltage & -temp
protections



MIL-STD 704F,
461F, 810G,
1275D



High reliability
modular design



Input voltage range:

10 – 45V

18 – 45V

Output power:

150W

300W

450W

600W

800W

Dimensions:

3U (3.9 x 6.6 x 1.0in)

A complete list of SOSA power supplies are available at vicorpower.com/sosa

Vicor: Enabling a competitive advantage

High-performance modular power systems achieve higher levels of flexibility and scalability than ground-up custom designs. Our continual advances in power distribution architectures, conversion topologies and packaging technology will keep you ahead in system efficiency and density, converting and managing power from the source to the point-of-load. www.vicorpower.com/defense-aero

Generating complete power systems

The screenshot shows the 'Power System Designer' interface. At the top, it says 'VICOR Power System Designer'. Below that, a green bar says 'Show me pricing for 100 power systems'. The main section is titled 'Enter your power requirements'. It has two columns for 'Output 1' and 'Output 2'. Each column has input fields for 'min input', 'nom input', and 'max input' (all set to 400V_{DC}). Output 1 has a '100W' power requirement and '48V nom output'. Output 2 has a '200W' power requirement and '24V nom output'. There are buttons for 'AC', 'DC', 'Regulated', and 'Fixed Ratio'. At the bottom of the form are buttons for 'ADD ANOTHER OUTPUT', 'UPDATE SOLUTIONS', and 'Reset'. Below the form is a 'Recommended solutions' section with a table of results.

Figure of merit	Component quantity	Total footprint (cm ²)	Front-end footprint (cm ²)	Point-of-load footprint (cm ²)	Total efficiency (%)	Front-end efficiency (%)	Point-of-load efficiency (%)	Price each for 100 power systems
Option 1								
Best Fit	4	11	7	4	93.0	96.1	96.8	\$107 to \$122
Lowest Price								
Smallest Footprint								
Option 2								
Highest Efficiency	4	19	14	4	93.4	96.6	94.5	\$244.04

Just enter a few specs to design your next power system

Designing your power system in a single location — up to 75% faster than traditional methods — is as easy as entering your input and output power as well as your basic system requirements. The Power System Designer is one of the Vicor web-based tools that makes it easy for you to build flexible, efficient and cost-effective power systems that get you to market faster.

- Instant performance analysis for recommended solutions
- Access an infinite number of products and technical specs
- Evaluate power chains electrically and mechanically
- Prioritize solutions by efficiency, component count, cost, footprint and recommended best fit
- Save, export and share a final BOM or power system

Start your next design at www.vicorpower.com/psd

